



PRODUCT CERTIFICATE

No.: CQC16002152146

NAME AND ADDRESS OF THE APPLICANT

KEMET Electronics Corporation
2835 KEMET way 29681 Simpsonville - US

NAME AND ADDRESS OF THE MANUFACTURER

KEMET Electronics Corporation
2835 KEMET way 29681 Simpsonville - US

NAME AND ADDRESS OF THE FACTORY

Shanghai Arcotronics Components & Machineries Co., Ltd., (V010304)
55 Taifeng Road, Anting Town, Jiading District, 201814 Shanghai, China

NAME, MODEL AND SPECIFICATION

High Frequency High Voltage Resonant Induction Heating Capacitor
R75 1000Vdc/400Vac 0.1 μ F-1 μ F J ($\pm 5\%$)、K ($\pm 10\%$)、M ($\pm 20\%$) 50kHz 55/105/56 SH

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T3984.1-2004;GB/T3984.2-2004

CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules CQC13-461241-2009.

Date of issue: Sep.20,2016

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

President:


Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0089879



产品认证证书

证书编号: CQC16002152146

申请人名称及地址

KEMET Electronics Corporation
2835 KEMET way 29681 Simpsonville - US 美国

制造商名称及地址

KEMET Electronics Corporation
2835 KEMET way 29681 Simpsonville - US 美国

生产企业名称及地址

上海阿可电子机械制造有限公司 (V010304)
上海市嘉定区安亭镇泰丰路55号

产品名称和系列、规格、型号

高频高压谐振感应加热电容器 (电磁炉用电容器)

R75 1000Vdc/400Vac 0.1 μ F-1 μ F J ($\pm 5\%$)、K ($\pm 10\%$)、M ($\pm 20\%$) 50kHz 55/105/56 SH

产品标准和技术要求

GB/T3984.1-2004; GB/T3984.2-2004

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC13-461241-2009认证规则的要求, 特发此证。

发证日期: 2016年09月20日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任: _____



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0089879