

VERIFICATION

No. 408932-1

Type of equipment: **Pulse Capacitor**

Document holder: **Evox Rifa AB
Box 945
391 29 Kalmar
SWEDEN**

Manufacturer: **Evox Rifa AB
Box 945
391 29 Kalmar
SWEDEN**

Type designation: **PHE450**

Technical data: **250, 400, 630, 1000, 1600, 2000, 2500VDC / 180, 250,
300/400, 375/600, 650, 700, 900VAC.
0.00033-6.8uF ± 5%. Climatic category 55/105/56**

Samples of the Pulse Capacitors, bigger than 1750mm³, have been tested according to the standard IEC 60065, clause 14.2.5 without any remarks.

Passive flammability test, category B, for capacitors bigger than 1750mm³.

The capacitors are manufactured in the Evox Rifa factories in Kalmar Sweden, Batam Indonesia or Suomussalmi Finland.

Standards used for showing compliance with the requirements:

Standards:

**IEC 60065:1999, clause 14.2.5
IEC 60384-1:1982, clause 4.38
IEC 60695-2-2:1980**

Stockholm
12 aug -04

Intertek Semko AB
Luminaires and Power Supplies



Fredrik Wennersten