


# Licence for



## CENELEC ENEC Agreement Licence Ref. No. SE/0140-4E

<b>Product:</b>	<b>Capacitor for radio interference suppression</b>
<b>Type designation:</b>	PHE 840*
<b>Test Report No.</b>	1611304STO-001,-002+1415512STO-001
<b>Licence holder:</b>	KEMET Electronics Oy Lars Sonckin kaari 16 FI-02600 Espoo FINLAND
<b>The product complies with the standard(s):</b>	EN 60384-14:2013
<b>Licence holder is authorized to use the mark with the following limitations:</b>	-
<b>Date of expiry:</b>	6 July 2021

### Additional information in Appendix

<i>Certification Body</i>	Intertek Semko AB, Product Certification	<i>Place</i>	Kista - Stockholm
<i>Signed</i>	 Bo Berglöf	<i>Date</i>	6 July 2016
<i>Internal reference:</i>	SUL		

This Licence is the result of testing a sample of the product submitted, in accordance with the provisions of the relevant specific standard. A copy of the Licence shall be filed in the place of manufacturing. The Licence has been established by a body which is a signatory to the ENEC Agreement ratified by CENELEC Marks Committee on 10 April 1992.

## APPENDIX

### CENELEC ENEC Agreement Licence Ref. No. SE/0140-4E

Test Report No. 1611304STO-001,-002+1415512STO-001

---

#### Technical data

Type designation	PHE 840 M
Rated voltage	275VAC
Class and sub-class	X2
Capacitance	0.01 – 10uF
Tolerance	±10%, ±20%
Climataic category	55/105/56/B
Trade mark	RIFA
Product information	Fulfils standard IEC 60384-14:2013

Type designation	PHE 840 E
Rated voltage	300VAC
Class and sub-class	X2
Capacitance	0.01 – 10uF
Tolerance	±10%, ±20%
Climataic category	55/105/56/B
Trade mark	RIFA
Product information	Fulfils standard IEC 60384-14:2013

Additional information:

0.01 – 3.3uF manufacturing site PT KEMET Electronics Indonesia  
0.47 – 10uF manufacturing site KEMET Electronics Oy and Shanghai Arcotronics Components & Machinerics Co.,Ltd

---

6 July 2016

**Intertek Semko AB**

Torshamnsgatan 43, Box 1103, SE-164 22 Kista, Sweden  
Telephone +46 8 750 00 00, Fax +46 8 750 60 30, www.sweden.intertek-etlsemko.com  
Registered in Sweden: No SE556024059901, Registered office: As address



**Manufacturing site(s):**

PT KEMET Electronics Indonesia  
Jalan Beringin Lot 325  
Batamindo Industrial Park  
Mukakuning, Batam 29433  
INDONESIA

KEMET Electronics Oy  
Siikarannantie 3  
FI-89600 Suomussalmi  
FINLAND

Shanghai Arcotronics Components &  
Machineries Co.,Ltd  
55 Taifeng Road, Anting  
Jiading, 201814, Shanghai  
CHINA

This certificate replaces previously issued ref. No. SE/0140-4D dated 15 November 2012 and SE/0140-39 dated 7 May 2015.

A new certificate has been issued on account of updated standard and combined certificates.

6 July 2016

**Intertek Semko AB**

Torshamnsgatan 43, Box 1103, SE-164 22 Kista, Sweden  
Telephone +46 8 750 00 00, Fax +46 8 750 60 30, [www.sweden.intertek-etlsemko.com](http://www.sweden.intertek-etlsemko.com)  
Registered in Sweden: No SE556024059901, Registered office: As address

