



# PRODUCT CERTIFICATE

No.: CQC15001128704

## NAME AND ADDRESS OF THE APPLICANT

KEMET Electronics Corporation  
2835 KEMET way 29681 Simpsonville - US

## NAME AND ADDRESS OF THE MANUFACTURER

KEMET Electronics Corporation  
2835 KEMET way 29681 Simpsonville - US

## NAME AND ADDRESS OF THE FACTORY

KEMET Electronics Bulgaria EAD (V010800)  
267, Tsar Osvoboditel str. 2500 Kyustendil, Bulgaria

## NAME, MODEL AND SPECIFICATION

Fixed capacitors for electromagnetic interference suppression

See Appendix

## THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

IEC60384-14:2005

## CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules  
CQC11-471112-2015.

Date of issue: Jun.30,2015

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing  
certification body until the expiry date.

President: \_\_\_\_\_

Wang Kejiao



## CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China  
<http://www.cqc.com.cn>

C 0065579



# 产品认证证书

证书编号: CQC15001128704

## 申请人名称及地址

基美电子有限公司  
2835 KEMET way 29681 Simpsonville - US 美国

## 制造商名称及地址

基美电子有限公司  
2835 KEMET way 29681 Simpsonville - US 美国

## 生产企业名称及地址

基美电子保加利亚有限公司 (V010800)  
267, Tsar Osvoboditel str. 2500 Kyustendil, Bulgaria 保加利亚

## 产品名称和系列、规格、型号

抑制电源电磁干扰用固定电容器

见附件

## 产品标准和技术要求

IEC60384-14: 2005

## 认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC11-471112-2015认证规则的要求, 特发此证。

发证日期: 2015年06月30日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任: \_\_\_\_\_



## 中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0065579



# 产品认证证书

附录:

第 1 页 共 1 页

证书编号: CQC15001128704

纸号: 65579

R. 41 0.001  $\mu$ F - 1  $\mu$ F  $\pm$  5%,  $\pm$  10%,  $\pm$  20% Y2/X1 300Vac 50/60Hz 40/110/56 C  
( $\leq$ 1750mm<sup>3</sup>) and 40/110/56 B ( $>$ 1750mm<sup>3</sup>)

注: 此附录与证书同时使用时有效。

主任: \_\_\_\_\_



## 中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>