



General Information	
Style	Metal Sealed
Description	Metal Sealed Type Multilayer Piezoelectric Actuators
RoHS	With Exemptions
SCIP Number	c64eed42-9f3b-4f55-976e-a799ec5ecf68
Notes	Without Flange, V groove.
REACH	SVHC (PZT – CAS 12626-81-2)

Specifications	
Series	AHB
Displacement	68um +/-15um
Voltage DC	150 VDC
Capacitance	32 uF
Capacitance Tolerance	20%
Resonant Frequency	12 kHz
Generated Force	3000 N
Insulation Resistance	2 MOhms
Temperature Range	-25/+85°C

Click [here](#) for the 3D model.

Dimensions	
D	20mm +/-0.3mm
L	65.4mm +/-0.5mm
LL	142mm +/-5mm

Packaging Specifications	
Typical Component Weight	76
Packaging	Bulk
Packaging Quantity	1