



# PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC12001081971

## NAME AND ADDRESS OF THE APPLICANT

KEMET Electronics Corporation  
2835 KEMET way, Simpsonville, SC 29681, United States of America

## NAME AND ADDRESS OF THE MANUFACTURER

KEMET Electronics Corporation  
2835 KEMET way, Simpsonville, SC 29681, United States of America

## NAME AND ADDRESS OF THE FACTORY

PT. KEMET Electronics Indonesia (V005505)  
BATAMINDO INDUSTRIAL PARK, LOT325,KEL MUKA KUNING KEC, Sei Beduk, BATAM,INDONESIA

## PRODUCT NAME, MODEL AND SPECIFICATION

Fixed capacitors for electromagnetic interference suppression  
F881 系列 0.001 to 1uF  $\pm 5\%$ ,  $\pm 10\%$ ,  $\pm 20\%$ ; Y2; 300V; 50/60Hz; 40/110/56 C,55/110/56 C ( $\leq 1750\text{mm}^3$ )  
and 40/110/56 B,55/110/56 B ( $> 1750\text{mm}^3$ )

## THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

IEC60384-14:2013+AMD1:2016

## TYPE OF CERTIFICATION SCHEMES

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471112-2015 .

Valid from: Sep.26,2019

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.

Date of original issued: Oct.29,2012

President: \_\_\_\_\_

Lu Mei



## CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China  
<http://www.cqc.com.cn>

C 0155831



# 产品认证证书

证书编号: CQC12001081971

## 申请人名称及地址

KEMET Electronics Corporation  
2835 KEMET way, Simpsonville, SC 29681, 美国

## 制造商名称及地址

KEMET Electronics Corporation  
2835 KEMET way, Simpsonville, SC 29681, 美国

## 生产企业名称及地址

PT. KEMET Electronics Indonesia (V005505)  
BATAMINDO INDUSTRIAL PARK, LOT325, KEL MUKA KUNING KEC, Sei Beduk, BATAM,  
印度尼西亚

## 产品名称和系列、规格、型号

抑制电源电磁干扰用固定电容器

F881 系列 0.001 to 1uF  $\pm 5\%$ ,  $\pm 10\%$ ,  $\pm 20\%$ ; Y2; 300V; 50/60Hz; 40/110/56 C, 55/110/56 C  
( $\leq 1750\text{mm}^3$ ) 或 40/110/56 B, 55/110/56 B ( $> 1750\text{mm}^3$ )

## 产品标准和技术要求

IEC60384-14:2013+AMD1:2016

## 认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-471112-2015 认证规则的要求, 特发此证。

发证日期: 2019 年 09 月 26 日

本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2012 年 10 月 29 日

主任: \_\_\_\_\_

陆楠



## 中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

C 0155831