

FOWX8.E97797 - FIXED CAPACITORS FOR USE IN ELECTRONIC EQUIPMENT CERTIFIED FOR CANADA - COMPONENT

Fixed Capacitors for Use in Electronic Equipment Certified for Canada - Component

See General Information for Fixed Capacitors for Use in Electronic Equipment Certified for Canada - Component

KEMET ELECTRONICS ITALIA SRL

E97797

Via Sagittario 1/3

40037 Sasso Marconi, BO ITALY




Fixed Capacitors

Type Dsg	Capacitor Class	Voltage Rating (V)	Capacitance (μF) (Tolerance)@	Resistance for RC Devices (ohms)	Lower Temp (°C)	Upper Temp (°C)
<i>F861 and F862</i>	X2	310 ac	0.001~10 μF/+/-20%	—	-40	110
<i>F881</i>	Y2	300 ac	0.001~1 μF/+/-20%	—	-40	110
<i>F873</i>	X1	760 ac	0.01~1.8 μF/+/-20%	—	-40	110
<i>F872</i>	X1	480 ac	0.001~3.5 μF/+/-20%	—	-40	110
<i>F871</i>	X1	330 ac	0.001~12 μF/+/-20%	—	-40	110
<i>R.46 and F863</i>	X2	275/300/310 ac	0.01~10 μF/+/-20%	—	-40	110
<i>R.46</i>	X2	275/300/310 ac	0.01~1 μF/+/-20%	—	-40	125
<i>R.41</i>	X1/Y2	300 ac	0.001~1 μF/+/-20%	—	-40	110
<i>R.47</i>	X1/X2	440 ac	0.0022~3.9 μF/+/-20%	—	-40	110

R.49	X1/X2	310/330 ac	0.0047~6.8 μ F/+/-20%	—	-40	110
1.43	X2	275 ac	0.01~2.2 μ F/+/-20%	10-1000 ohms	-40	100
SMP253	X2	250 ac	0.001~0.0047 μ F/+/-20%	—	-40	100

@ The model code may be followed by M for +/-20%. K for +/-10%. J for +/-5%.

Suitable for use with special enclosure only.

Marking: Company name or trademarks "Arcotronics", Arco-I, Arco), , , type designation and Recognized Component Mark for Canada .

Last Updated on 2019-02-21

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2019 UL LLC"