



T520 Series - KEMET Organic Conductive Polymer Capacitor

Product Release 1/31/06

Component Outline Drawing



Component Marking



* 510 = 10th week of 2005

Case Codes		Component Dimensions					
		L	W	H	K Min	F ± 0.1	S ± 0.3
KEMET	EIA						
A	3216-18	3.2±0.2	1.6±0.2	1.6±0.2	0.7	1.2	0.8
B	3528-20	3.5±0.2	2.8±0.2	1.9±0.1	0.9	2.2	0.8
C	6032-28	6.0±0.3	3.2±0.3	2.5±0.3	1.2	2.2	1.3
W	7343-15	7.3±0.3	4.3±0.3	1.5 max	0.6	2.4	1.3
V	7343-19	7.3±0.3	4.3±0.3	1.9 max	0.9	2.4	1.3
D	7343-31	7.3±0.3	4.3±0.3	2.8±0.3	1.3	2.4	1.3
Y	7343-40	7.3±0.3	4.3±0.3	4.0 max	1.3	2.4	1.3
X	7343-43	7.3±0.3	4.3±0.3	4.0±0.3	2.1	2.4	1.3
T	3528-12	3.5±0.2	2.8±0.2	1.2 max	0.3	2.2	0.8

Part Number and Electrical Specification Table

KEMET Part Number	Case	Cap (µF)	Voltage (V)	DCL V _R (µA)	DF 120Hz (%)	ESR, 100kHz (mΩ)	Ripple Current (Arms) @ 100 kHz	
							delta T=20°C @ -55°C to 85°C	delta T=2°C @ 105°C
T520T336M008A*E080	T/3528-12	33	8	26	8	80	0.9	0.3
T520A106M010A*E080	A/3216-18	10	10	10	8	80	1.0	0.3
T520A156M010A*E080	A/3216-18	15	10	15	8	80	1.0	0.3
T520T336M010A*E080	T/3528-12	33	10	33	8	80	0.9	0.3

* Insert "T" for 100% tin (Sn) termination or "H" for tin/lead (Sn/Pb) termination