


- Metallized polyphenylene sulphide (PPS) SMD
- Miniature size naked capacitor
- Low profile
- Wound construction
- According to IEC 60384-20

TYPICAL APPLICATIONS

Timing, filtering. Memory capacitor. High stability and accuracy. High temperature use.

CONSTRUCTION

Polyphenylene sulphide (PPS) film capacitor for surface mounting.



TECHNICAL DATA

Rated voltage U_R , VDC	50	100	250	400
Rated voltage U_R , VAC	30	63	160	200
Capacitance range, nF	1 - 560	1 - 180	1 - 68	1 - 22

Capacitance tolerance $\pm 10\%$, $\pm 5\%$ standard; $\pm 2.5\%$, $\pm 2\%$ on request.

Category temperature range -55°C to $+125^\circ\text{C}$.

Rated temperature $+100^\circ\text{C}$

Voltage derating The rated voltage should be decreased with $1.5\%/^\circ\text{C}$ from $+125^\circ\text{C}$ to 175°C . No derating from $+100^\circ\text{C}$ to $+125^\circ\text{C}$.

Climatic category 55/125/56

Voltage proof $1.6 \times U_R$, 60s


Insulation resistance Minimum value between terminals
Measured at $+20^\circ\text{C}$ according to IEC 60384-20

	$C \leq 0.56 \mu\text{F}$	
$U_R \leq 100 \text{ V}$	15 000 $\text{M}\Omega$	
$U_R > 100 \text{ V}$	30 000 $\text{M}\Omega$	


Dissipation factor Max values at $+23^\circ\text{C}$

	$C \leq 100\text{nF}$	$100\text{nF} < C \leq 560 \text{ nF}$
1 kHz	0.15 %	0.15 %
10 kHz	0.25 %	0.25 %
100 kHz	0.50 %	0.60 %

Pulse rise time The capacitors can withstand an unlimited number of pulses with a dU/dt according to article table. For voltages (U) lower than the rated voltage (U_R), the specified dU/dt can be multiplied by U_R/U .



Typical capacitance vs temperature at 1 kHz




Typical dissipation factor vs temperature at 1 kHz

RECOMMENDED SOLDERING CONDITIONS


Reflow soldering temperature measured on the top body surface of the component

Preheating temperature should be less than 170°C . The time above 217°C should be less than 50 s. The peak temperature must not exceed 240°C .



Electrode temperature, Wave soldering

The recommended preheating temperature is 90°C , max 130°C . The peak temperature 260°C may be applied for 2 + 3 s max. Evox Rifa recommends wave soldering for SMW parts with up to $H = 2 \text{ mm}$.



Recommended wave soldering profile

MARKING

- Rated capacitance
- Capacitance tolerance code
- Rated voltage code
- Capacitor type S for SMW
- Manufacturing date code according to IEC 60062 (year, month)

ORDERING INFORMATION

See article table and page 10 for options and article code construction.

ARTICLE TABLE

Capacitance µF	Size code	Dimensions in mm		Max dU/dt V/µs	Article code	Capacitance µF	Size code	Dimensions in mm		Max dU/dt V/µs	Article code
		B	H					B	H		
50 VDC/30 VAC						50 VDC/30 VAC					
CHIP LENGTH 5.7 MM CODE 2220						CHIP LENGTH 7.3 MM CODE 2824					
0.0010	J91	5.0	2.0	20	SMW5.7 102K50J91 TR12	0.33	K93	6.0	2.7	8	SMW7.3 334K50K93 TR12
0.0012	J91	5.0	2.0	20	SMW5.7 122K50J91 TR12	0.39	K95	6.0	3.2	8	SMW7.3 394K50K95 TR12
0.0015	J91	5.0	2.0	20	SMW5.7 152K50J91 TR12	0.47	K95	6.0	3.2	8	SMW7.3 474K50K95 TR12
0.0018	J91	5.0	2.0	20	SMW5.7 182K50J91 TR12	0.56	K97	6.0	4.2	8	SMW7.3 564K50K97 TR12
0.0022	J91	5.0	2.0	20	SMW5.7 222K50J91 TR12	100 VDC/63 VAC					
0.0027	J91	5.0	2.0	20	SMW5.7 272K50J91 TR12	CHIP LENGTH 5.7 MM CODE 2220					
0.0033	J91	5.0	2.0	20	SMW5.7 332K50J91 TR12	0.0010	J91	5.0	2.0	20	SMW5.7 102K100J91 TR12
0.0039	J91	5.0	2.0	20	SMW5.7 392K50J91 TR12	0.0012	J91	5.0	2.0	20	SMW5.7 122K100J91 TR12
0.0047	J91	5.0	2.0	20	SMW5.7 472K50J91 TR12	0.0015	J91	5.0	2.0	20	SMW5.7 152K100J91 TR12
0.0056	J91	5.0	2.0	20	SMW5.7 562K50J91 TR12	0.0018	J91	5.0	2.0	20	SMW5.7 182K100J91 TR12
0.0068	J91	5.0	2.0	20	SMW5.7 682K50J91 TR12	0.0022	J91	5.0	2.0	20	SMW5.7 222K100J91 TR12
0.0082	J91	5.0	2.0	20	SMW5.7 822K50J91 TR12	0.0027	J91	5.0	2.0	20	SMW5.7 272K100J91 TR12
0.010	J91	5.0	2.0	20	SMW5.7 103K50J91 TR12	0.0033	J91	5.0	2.0	20	SMW5.7 332K100J91 TR12
0.012	J91	5.0	2.0	20	SMW5.7 123K50J91 TR12	0.0039	J91	5.0	2.0	20	SMW5.7 392K100J91 TR12
0.015	J91	5.0	2.0	20	SMW5.7 153K50J91 TR12	0.0047	J91	5.0	2.0	20	SMW5.7 472K100J91 TR12
0.018	J91	5.0	2.0	15	SMW5.7 183K50J91 TR12	0.0056	J91	5.0	2.0	20	SMW5.7 562K100J91 TR12
0.022	J91	5.0	2.0	15	SMW5.7 223K50J91 TR12	0.0068	J91	5.0	2.0	20	SMW5.7 682K100J91 TR12
0.027	J91	5.0	2.0	15	SMW5.7 273K50J91 TR12	0.0082	J91	5.0	2.0	20	SMW5.7 822K100J91 TR12
0.033	J91	5.0	2.0	15	SMW5.7 333K50J91 TR12	0.010	J91	5.0	2.0	20	SMW5.7 103K100J91 TR12
0.039	J91	5.0	2.0	15	SMW5.7 393K50J91 TR12	0.012	J91	5.0	2.0	20	SMW5.7 123K100J91 TR12
0.047	J91	5.0	2.0	15	SMW5.7 473K50J91 TR12	0.015	J91	5.0	2.0	20	SMW5.7 153K100J91 TR12
0.056	J91	5.0	2.0	15	SMW5.7 563K50J91 TR12	0.018	J91	5.0	2.0	15	SMW5.7 183K100J91 TR12
0.068	J91	5.0	2.0	15	SMW5.7 683K50J91 TR12	0.022	J91	5.0	2.0	15	SMW5.7 223K100J91 TR12
0.082	J91	5.0	2.0	10	SMW5.7 823K50J91 TR12	0.027	J91	5.0	2.0	15	SMW5.7 273K100J91 TR12
0.10	J91	5.0	2.0	10	SMW5.7 104K50J91 TR12	0.033	J91	5.0	2.0	15	SMW5.7 333K100J91 TR12
0.12	J91	5.0	2.0	10	SMW5.7 124K50J91 TR12	0.039	J91	5.0	2.0	15	SMW5.7 393K100J91 TR12
0.15	J91	5.0	2.0	10	SMW5.7 154K50J91 TR12	0.047	J91	5.0	2.0	15	SMW5.7 473K100J91 TR12
0.18	J93	5.0	3.0	10	SMW5.7 184K50J93 TR12	0.056	J91	5.0	2.0	15	SMW5.7 563K100J91 TR12
0.22	J93	5.0	3.0	10	SMW5.7 224K50J93 TR12	0.068	J91	5.0	2.0	15	SMW5.7 683K100J91 TR12
0.27	J93	5.0	3.0	10	SMW5.7 274K50J93 TR12	0.082	J93	5.0	3.0	15	SMW5.7 823K100J93 TR12
0.33	J95	5.0	4.0	10	SMW5.7 334K50J95 TR12	0.10	J93	5.0	3.0	15	SMW5.7 104K100J93 TR12
CHIP LENGTH 7.3 MM CODE 2824						0.12	J95	5.0	4.0	15	SMW5.7 124K100J95 TR12
0.0022	K91	6.0	2.0	20	SMW7.3 222K50K91 TR12	0.15	J95	5.0	4.0	15	SMW5.7 154K100J95 TR12
0.0027	K91	6.0	2.0	20	SMW7.3 272K50K91 TR12	CHIP LENGTH 7.3 MM CODE 2824					
0.0033	K91	6.0	2.0	20	SMW7.3 332K50K91 TR12	0.0022	K91	6.0	2.0	20	SMW7.3 222K100K91 TR12
0.0039	K91	6.0	2.0	20	SMW7.3 392K50K91 TR12	0.0027	K91	6.0	2.0	20	SMW7.3 272K100K91 TR12
0.0047	K91	6.0	2.0	20	SMW7.3 472K50K91 TR12	0.0033	K91	6.0	2.0	20	SMW7.3 332K100K91 TR12
0.0056	K91	6.0	2.0	20	SMW7.3 562K50K91 TR12	0.0039	K91	6.0	2.0	20	SMW7.3 392K100K91 TR12
0.0068	K91	6.0	2.0	20	SMW7.3 682K50K91 TR12	0.0047	K91	6.0	2.0	20	SMW7.3 472K100K91 TR12
0.0082	K91	6.0	2.0	20	SMW7.3 822K50K91 TR12	0.0056	K91	6.0	2.0	20	SMW7.3 562K100K91 TR12
0.010	K91	6.0	2.0	20	SMW7.3 103K50K91 TR12	0.0068	K91	6.0	2.0	20	SMW7.3 682K100K91 TR12
0.012	K91	6.0	2.0	20	SMW7.3 123K50K91 TR12	0.0082	K91	6.0	2.0	20	SMW7.3 822K100K91 TR12
0.015	K91	6.0	2.0	20	SMW7.3 153K50K91 TR12	0.010	K91	6.0	2.0	20	SMW7.3 103K100K91 TR12
0.018	K91	6.0	2.0	20	SMW7.3 183K50K91 TR12	0.012	K91	6.0	2.0	20	SMW7.3 123K100K91 TR12
0.022	K91	6.0	2.0	20	SMW7.3 223K50K91 TR12	0.015	K91	6.0	2.0	20	SMW7.3 153K100K91 TR12
0.027	K91	6.0	2.0	15	SMW7.3 273K50K91 TR12	0.018	K91	6.0	2.0	20	SMW7.3 183K100K91 TR12
0.033	K91	6.0	2.0	15	SMW7.3 333K50K91 TR12	0.022	K91	6.0	2.0	20	SMW7.3 223K100K91 TR12
0.039	K91	6.0	2.0	15	SMW7.3 393K50K91 TR12	0.027	K91	6.0	2.0	15	SMW7.3 273K100K91 TR12
0.047	K91	6.0	2.0	15	SMW7.3 473K50K91 TR12	0.033	K91	6.0	2.0	15	SMW7.3 333K100K91 TR12
0.056	K91	6.0	2.0	15	SMW7.3 563K50K91 TR12	0.039	K91	6.0	2.0	15	SMW7.3 393K100K91 TR12
0.068	K91	6.0	2.0	15	SMW7.3 683K50K91 TR12	0.047	K91	6.0	2.0	15	SMW7.3 473K100K91 TR12
0.082	K91	6.0	2.0	8	SMW7.3 823K50K91 TR12	0.056	K91	6.0	2.0	15	SMW7.3 563K100K91 TR12
0.10	K91	6.0	2.0	8	SMW7.3 104K50K91 TR12	0.068	K91	6.0	2.0	15	SMW7.3 683K100K91 TR12
0.12	K91	6.0	2.0	8	SMW7.3 124K50K91 TR12	0.082	K91	6.0	2.0	15	SMW7.3 823K100K91 TR12
0.15	K91	6.0	2.0	8	SMW7.3 154K50K91 TR12	0.10	K93	6.0	2.7	15	SMW7.3 104K100K93 TR12
0.18	K91	6.0	2.0	8	SMW7.3 184K50K91 TR12						
0.22	K91	6.0	2.0	8	SMW7.3 224K50K91 TR12						
0.27	K91	6.0	2.0	8	SMW7.3 274K50K91 TR12						

ARTICLE TABLE

Capacitance µF	Size code	Dimensions in mm		Max dU/dt V/µs	Article code
		B	H		
		±0.4 max			

100 VDC/63 VAC

CHIP LENGTH 7.3 MM CODE 2824

0.12	K93	6.0	2.7	15	SMW7.3 124K100K93 TR12
0.15	K95	6.0	3.2	15	SMW7.3 154K100K95 TR12
0.18	K97	6.0	4.2	15	SMW7.3 184K100K97 TR12

250 VDC/160 VAC

CHIP LENGTH 5.7 MM CODE 2220

0.0010	J91	5.0	2.0	20	SMW5.7 102K250J91 TR12
0.0012	J91	5.0	2.0	20	SMW5.7 122K250J91 TR12
0.0015	J91	5.0	2.0	20	SMW5.7 152K250J91 TR12
0.0018	J91	5.0	2.0	20	SMW5.7 182K250J91 TR12
0.0022	J91	5.0	2.0	20	SMW5.7 222K250J91 TR12
0.0027	J91	5.0	2.0	20	SMW5.7 272K250J91 TR12
0.0033	J91	5.0	2.0	20	SMW5.7 332K250J91 TR12
0.0039	J91	5.0	2.0	20	SMW5.7 392K250J91 TR12
0.0047	J91	5.0	2.0	20	SMW5.7 472K250J91 TR12
0.0056	J91	5.0	2.0	20	SMW5.7 562K250J91 TR12
0.0068	J91	5.0	2.0	20	SMW5.7 682K250J91 TR12
0.0082	J91	5.0	2.0	20	SMW5.7 822K250J91 TR12
0.010	J91	5.0	2.0	20	SMW5.7 103K250J91 TR12
0.012	J91	5.0	2.0	20	SMW5.7 123K250J91 TR12
0.015	J91	5.0	2.0	20	SMW5.7 153K250J91 TR12
0.018	J93	5.0	3.0	20	SMW5.7 183K250J93 TR12
0.022	J93	5.0	3.0	20	SMW5.7 223K250J93 TR12
0.027	J93	5.0	3.0	20	SMW5.7 273K250J93 TR12
0.033	J95	5.0	4.0	20	SMW5.7 333K250J95 TR12

CHIP LENGTH 7.3 MM CODE 2824

0.0022	K91	6.0	2.0	20	SMW7.3 222K250K91 TR12
0.0027	K91	6.0	2.0	20	SMW7.3 272K250K91 TR12
0.0033	K91	6.0	2.0	20	SMW7.3 332K250K91 TR12
0.0039	K91	6.0	2.0	20	SMW7.3 392K250K91 TR12
0.0047	K91	6.0	2.0	20	SMW7.3 472K250K91 TR12
0.0056	K91	6.0	2.0	20	SMW7.3 562K250K91 TR12
0.0068	K91	6.0	2.0	20	SMW7.3 682K250K91 TR12
0.0082	K91	6.0	2.0	20	SMW7.3 822K250K91 TR12
0.010	K91	6.0	2.0	20	SMW7.3 103K250K91 TR12
0.012	K91	6.0	2.0	20	SMW7.3 123K250K91 TR12
0.015	K91	6.0	2.0	20	SMW7.3 153K250K91 TR12
0.018	K91	6.0	2.0	20	SMW7.3 183K250K91 TR12
0.022	K91	6.0	2.0	20	SMW7.3 223K250K91 TR12
0.027	K91	6.0	2.0	15	SMW7.3 273K250K91 TR12
0.033	K93	6.0	2.7	15	SMW7.3 333K250K93 TR12
0.039	K93	6.0	2.7	15	SMW7.3 393K250K93 TR12
0.047	K95	6.0	3.2	15	SMW7.3 473K250K95 TR12
0.056	K97	6.0	4.2	15	SMW7.3 563K250K97 TR12
0.068	K97	6.0	4.2	15	SMW7.3 683K250K97 TR12

Capacitance µF	Size code	Dimensions in mm		Max dU/dt V/µs	Article code
		B	H		
		±0.4 max			

400 VDC/200 VAC

CHIP LENGTH 5.7 MM CODE 2220

0.0010	J91	5.0	2.0	20	SMW5.7 102K400J91 TR12
0.0012	J91	5.0	2.0	20	SMW5.7 122K400J91 TR12
0.0015	J91	5.0	2.0	20	SMW5.7 152K400J91 TR12
0.0018	J91	5.0	2.0	20	SMW5.7 182K400J91 TR12
0.0022	J91	5.0	2.0	20	SMW5.7 222K400J91 TR12
0.0027	J91	5.0	2.0	20	SMW5.7 272K400J91 TR12
0.0033	J91	5.0	2.0	20	SMW5.7 332K400J91 TR12
0.0039	J91	5.0	2.0	20	SMW5.7 392K400J91 TR12
0.0047	J91	5.0	2.0	20	SMW5.7 472K400J91 TR12
0.0056	J93	5.0	3.0	20	SMW5.7 562K400J93 TR12
0.0068	J93	5.0	3.0	20	SMW5.7 682K400J93 TR12
0.0082	J93	5.0	3.0	20	SMW5.7 822K400J93 TR12
0.010	J93	5.0	3.0	20	SMW5.7 103K400J93 TR12
0.012	J95	5.0	4.0	20	SMW5.7 123K400J95 TR12
0.015	J95	5.0	4.0	20	SMW5.7 153K400J95 TR12

CHIP LENGTH 7.3 MM CODE 2824

0.0022	K91	6.0	2.0	20	SMW7.3 222K400K91 TR12
0.0027	K91	6.0	2.0	20	SMW7.3 272K400K91 TR12
0.0033	K91	6.0	2.0	20	SMW7.3 332K400K91 TR12
0.0039	K91	6.0	2.0	20	SMW7.3 392K400K91 TR12
0.0047	K91	6.0	2.0	20	SMW7.3 472K400K91 TR12
0.0056	K91	6.0	2.0	20	SMW7.3 562K400K91 TR12
0.0068	K91	6.0	2.0	20	SMW7.3 682K400K91 TR12
0.0082	K91	6.0	2.0	20	SMW7.3 822K400K91 TR12
0.010	K91	6.0	2.0	20	SMW7.3 103K400K91 TR12
0.012	K93	6.0	2.7	20	SMW7.3 123K400K93 TR12
0.015	K93	6.0	2.7	20	SMW7.3 153K400K93 TR12
0.018	K95	6.0	3.2	20	SMW7.3 183K400K95 TR12
0.022	K95	6.0	3.2	20	SMW7.3 223K400K95 TR12

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.