

METALLIZED POLYPROPYLENE

**MKP C4B Series**

**BOX CAPACITORS**  
**RoHS COMPLIANT**

**CAPACITORS**  
**FOR IGBT APPLICATIONS**

## C4B TERMINALS STYLES

All dimensions are in mm

	<table border="1"> <thead> <tr> <th colspan="3">Style A</th> </tr> </thead> <tbody> <tr> <td>L</td> <td>41.5 ÷ 42.5</td> <td>57.5</td> </tr> <tr> <td>P</td> <td>25.5</td> <td>41.0</td> </tr> <tr> <td>a</td> <td>21.5</td> <td>37.0</td> </tr> <tr> <td>b</td> <td>29.5</td> <td>45.0</td> </tr> <tr> <td>P1</td> <td>10.5</td> <td>25.0</td> </tr> </tbody> </table>	Style A			L	41.5 ÷ 42.5	57.5	P	25.5	41.0	a	21.5	37.0	b	29.5	45.0	P1	10.5	25.0
Style A																			
L	41.5 ÷ 42.5	57.5																	
P	25.5	41.0																	
a	21.5	37.0																	
b	29.5	45.0																	
P1	10.5	25.0																	
	<table border="1"> <thead> <tr> <th colspan="3">Style B</th> </tr> </thead> <tbody> <tr> <td>L</td> <td>41.5 ÷ 42.5</td> <td>57.5</td> </tr> <tr> <td>P</td> <td>22.0</td> <td>37.0</td> </tr> <tr> <td>a</td> <td>16.0</td> <td>31.0</td> </tr> <tr> <td>b</td> <td>28.0</td> <td>43.0</td> </tr> <tr> <td>P1</td> <td>6.0</td> <td>21.0</td> </tr> </tbody> </table>	Style B			L	41.5 ÷ 42.5	57.5	P	22.0	37.0	a	16.0	31.0	b	28.0	43.0	P1	6.0	21.0
Style B																			
L	41.5 ÷ 42.5	57.5																	
P	22.0	37.0																	
a	16.0	31.0																	
b	28.0	43.0																	
P1	6.0	21.0																	
	<table border="1"> <thead> <tr> <th colspan="3">Style D</th> </tr> </thead> <tbody> <tr> <td>L</td> <td>41.5 ÷ 42.5</td> <td>57.5</td> </tr> <tr> <td>P</td> <td>22.0</td> <td>37.0</td> </tr> <tr> <td>a</td> <td>18.0</td> <td>33.0</td> </tr> <tr> <td>b</td> <td>26.0</td> <td>41.0</td> </tr> <tr> <td>P1</td> <td>6.0</td> <td>21.0</td> </tr> </tbody> </table>	Style D			L	41.5 ÷ 42.5	57.5	P	22.0	37.0	a	18.0	33.0	b	26.0	41.0	P1	6.0	21.0
Style D																			
L	41.5 ÷ 42.5	57.5																	
P	22.0	37.0																	
a	18.0	33.0																	
b	26.0	41.0																	
P1	6.0	21.0																	

	<table border="1"> <thead> <tr> <th colspan="3">Style E</th> </tr> </thead> <tbody> <tr> <td>B</td> <td>20.0</td> <td>22.0</td> </tr> <tr> <td>P</td> <td>33.0</td> <td>35.0</td> </tr> <tr> <td>a</td> <td>31.0</td> <td>33.0</td> </tr> <tr> <td>b</td> <td>35.0</td> <td>37.0</td> </tr> <tr> <td>P1</td> <td>46.0</td> <td>48.0</td> </tr> </tbody> </table>	Style E			B	20.0	22.0	P	33.0	35.0	a	31.0	33.0	b	35.0	37.0	P1	46.0	48.0
Style E																			
B	20.0	22.0																	
P	33.0	35.0																	
a	31.0	33.0																	
b	35.0	37.0																	
P1	46.0	48.0																	
	<table border="1"> <thead> <tr> <th colspan="3">Style F</th> </tr> </thead> <tbody> <tr> <td>L</td> <td>41.5 ÷ 42.5</td> <td>57.5</td> </tr> <tr> <td>P</td> <td>22.0</td> <td>37.0</td> </tr> <tr> <td>a</td> <td>16.0</td> <td>31.0</td> </tr> <tr> <td>b</td> <td>28.0</td> <td>43.0</td> </tr> <tr> <td>P1</td> <td>6.0</td> <td>21.0</td> </tr> </tbody> </table> <p>c: could be 1.9 or 3.5 mm</p>	Style F			L	41.5 ÷ 42.5	57.5	P	22.0	37.0	a	16.0	31.0	b	28.0	43.0	P1	6.0	21.0
Style F																			
L	41.5 ÷ 42.5	57.5																	
P	22.0	37.0																	
a	16.0	31.0																	
b	28.0	43.0																	
P1	6.0	21.0																	
	<table border="1"> <thead> <tr> <th colspan="3">Style G</th> </tr> </thead> <tbody> <tr> <td>L</td> <td>41.5 ÷ 42.5</td> <td>57.5</td> </tr> <tr> <td>P</td> <td>22.0</td> <td>37.0</td> </tr> <tr> <td>a</td> <td>4.0</td> <td>4.0</td> </tr> <tr> <td>P1</td> <td>10.5</td> <td>25.0</td> </tr> </tbody> </table>	Style G			L	41.5 ÷ 42.5	57.5	P	22.0	37.0	a	4.0	4.0	P1	10.5	25.0			
Style G																			
L	41.5 ÷ 42.5	57.5																	
P	22.0	37.0																	
a	4.0	4.0																	
P1	10.5	25.0																	
	<table border="1"> <thead> <tr> <th colspan="3">Style H</th> </tr> </thead> <tbody> <tr> <td>L</td> <td>41.5 ÷ 42.5</td> <td>57.5</td> </tr> <tr> <td>P</td> <td>25.5</td> <td>41.0</td> </tr> <tr> <td>a</td> <td>21.5</td> <td>37.0</td> </tr> <tr> <td>b</td> <td>29.5</td> <td>45.0</td> </tr> <tr> <td>P1</td> <td>10.5</td> <td>25.0</td> </tr> </tbody> </table>	Style H			L	41.5 ÷ 42.5	57.5	P	25.5	41.0	a	21.5	37.0	b	29.5	45.0	P1	10.5	25.0
Style H																			
L	41.5 ÷ 42.5	57.5																	
P	25.5	41.0																	
a	21.5	37.0																	
b	29.5	45.0																	
P1	10.5	25.0																	

	<table border="1"> <thead> <tr> <th colspan="3">Style M</th> </tr> </thead> <tbody> <tr> <td>L</td> <td>41.5 ÷ 42.5</td> <td>57.5</td> </tr> <tr> <td>P</td> <td>25.5</td> <td>41.0</td> </tr> <tr> <td>a</td> <td>21.5</td> <td>37.0</td> </tr> <tr> <td>b</td> <td>29.5</td> <td>45.0</td> </tr> <tr> <td>P1</td> <td>10.5</td> <td>25.0</td> </tr> </tbody> </table>	Style M			L	41.5 ÷ 42.5	57.5	P	25.5	41.0	a	21.5	37.0	b	29.5	45.0	P1	10.5	25.0
Style M																			
L	41.5 ÷ 42.5	57.5																	
P	25.5	41.0																	
a	21.5	37.0																	
b	29.5	45.0																	
P1	10.5	25.0																	
	<table border="1"> <thead> <tr> <th colspan="3">Style T</th> </tr> </thead> <tbody> <tr> <td>B</td> <td>20.0</td> <td>22.0</td> </tr> <tr> <td>P</td> <td>33.0</td> <td>35.0</td> </tr> <tr> <td>a</td> <td>31.0</td> <td>33.0</td> </tr> <tr> <td>b</td> <td>34.0</td> <td>36.0</td> </tr> <tr> <td>P1</td> <td>46.0</td> <td>48.0</td> </tr> </tbody> </table>	Style T			B	20.0	22.0	P	33.0	35.0	a	31.0	33.0	b	34.0	36.0	P1	46.0	48.0
Style T																			
B	20.0	22.0																	
P	33.0	35.0																	
a	31.0	33.0																	
b	34.0	36.0																	
P1	46.0	48.0																	
	<table border="1"> <thead> <tr> <th colspan="3">Style W</th> </tr> </thead> <tbody> <tr> <td>L</td> <td>41.5 ÷ 42.5</td> <td>57.5</td> </tr> <tr> <td>P</td> <td>22.0</td> <td>37.0</td> </tr> <tr> <td>a</td> <td>17.0</td> <td>32.0</td> </tr> <tr> <td>b</td> <td>27.0</td> <td>42.0</td> </tr> <tr> <td>P1</td> <td>6.0</td> <td>21.0</td> </tr> </tbody> </table>	Style W			L	41.5 ÷ 42.5	57.5	P	22.0	37.0	a	17.0	32.0	b	27.0	42.0	P1	6.0	21.0
Style W																			
L	41.5 ÷ 42.5	57.5																	
P	22.0	37.0																	
a	17.0	32.0																	
b	27.0	42.0																	
P1	6.0	21.0																	
	<table border="1"> <thead> <tr> <th colspan="3">Style X</th> </tr> </thead> <tbody> <tr> <td>L</td> <td>41.5 ÷ 42.5</td> <td>57.5</td> </tr> <tr> <td>P</td> <td>22.0</td> <td>37.0</td> </tr> <tr> <td>a</td> <td>20.5</td> <td>35.5</td> </tr> <tr> <td>b</td> <td>23.5</td> <td>38.5</td> </tr> <tr> <td>P1</td> <td>6.0</td> <td>21.0</td> </tr> </tbody> </table>	Style X			L	41.5 ÷ 42.5	57.5	P	22.0	37.0	a	20.5	35.5	b	23.5	38.5	P1	6.0	21.0
Style X																			
L	41.5 ÷ 42.5	57.5																	
P	22.0	37.0																	
a	20.5	35.5																	
b	23.5	38.5																	
P1	6.0	21.0																	

#### General Disclaimer

All product specifications, statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application.

#### Prototype Sample Disclaimer

The Customer acknowledges the following limitations of the prototype samples:

- (1) Prototype samples are manufactured from preliminary designs and manufacturing processes; may not represent final designs; have not been released for commercial use and are not subject to the same quality control procedures applicable to released products.
- (2) Prototype samples are not qualified parts and are provided "as-is" by KEMET Electronics Corporation, which specifically disclaims any and all warranties and guarantees, explicit or implied, including, without limitation, the warranties of merchantability and fitness for a particular purpose or use.
- (3) Prototype samples are not intended for commercial use; are provided for engineering evaluation only and are not recommended for use in the Customer's production line.
- (4) The Customer assumes the risk of any and all uses that the Customer makes of the prototype samples.

KEMET's product warranty is set forth at [www.kemet.com](http://www.kemet.com) under Terms and Conditions of Sale.

COPYRIGHT KEMET ELECTRONICS CORPORATION 2013, all rights reserved.