



Dimensions	
D	25mm +1mm
L	50mm +2mm
S	10mm +/-0.5mm
F	2mm +/-0.1mm

Packaging Specifications	
Lead	2 Pin
Packaging	Bulk, Box
Packaging Quantity	100

General Information	
Series	HVZ
Description	Radial Cylindrical Double Layer Capacitor
RoHS	Yes
AEC-Q200	No
Typical Component Weight	28 g

Specifications	
Capacitance	100 F
Capacitance Tolerance	30%
Voltage DC	2.7 VDC
Temperature Range	-25/+60°C
Rated Temperature	60°C
ESR	30 mOhms (1kHz)
Discharge Current	81 mAmps (30 Minutes After Charging)